DATA SHEET TB O6a

BR 06a · PTFE-lined Micro-flow Valve

Single-seated Micro-flow Valve • DIN-Version

CE

Applications

PTFE-lined control valve for severely corrosive media, especially for low flow rates and chemical processes:

- Nominal size DN 6 to DN 15
- Nominal pressure PN 10
- Temperature range -10°C to +150°C

The control valve consists of a micro-flow valve with PTFE lining and either a pneumatic actuator or hand-operated actuator. The valve is designed according to the modular-assembly principle and can be combined with various options and has the following features:

- Valve body made of PTFE reinforced by a casing of spheroidal graphite iron EN-JS 1049 with a plastic coating
- Exchangeable PTFE seat and PTFE plug
- Stem sealed by a PTFE bellows
- Additional PTFE backup packing
- Exchangeable actuator
- Additional equipment can be added in according to DIN EN 60534 and NAMUR Recommendation

Versions

The BR 06a Micro-flow Valve is available optionally in the following versions:

- With SAMSON pneumatic actuator
- With hand-operated actuator
- With actuators of other manufacturers on request

Special designs

- Lining made of compounds, e.g. conductive PTFE
- Valve plug and seat made of special materials (e.g. tantalum)







Table 1: List of parts

ltem	Description					
1	Basic body with internal casing					
2	Bonnet flange with Yoke					
3	Screw					
4	Bearing bushing					
5	Guide bushing					
6	O-ring					
7	O-ring					
8	Thrust washer					
9	Spring washer					
10	Stem					

ltem	Description					
11	Bellows					
12	V-ring packing					
13	Set of spring washers					
14	Seat					
15	Stuffing box					
16	Bearing bushing					
17	Nut					
18	Coupling					
19	Plug					
20	Cord					

Principle of operation

The process medium flows through the valve in the flow-to-open direction.

The valve plug position determines the cross-sectional area of flow between the seat (14) and the plug (19).

The valve plug (19) is connected over the stem (10) to the actuator stem.

The PTFE bellows (11) seals the area between the valve body (1) and stem (10).

In the standard version, the bellow unit is suitable for operating pressures (p2) up to 6 bar.

In addition, the Stem is sealed by a PTFE V-ring packing (12) which is spring supported by disc springs (13) positioned above the packing.

The PTFE seat (14) is screwed into the valve body (1) over a thread suitable for plastic.

i Note

Before using the valve in hazardous areas, check whether this is possible according to ATEX 2014/34/EU by referring to the operating instructions ► BA 01a.

Fail-safe position

Depending on how the pneumatic actuator is mounted to the valve, the valve has two fail-safe positions which become effective when the air pressure in the actuator is relieved or when the supply air fails:

• Fail-close valves:

Upon air failure, the valve is closed. The valve opens when the signal pressure increases, acting against the force of the springs.

• Fail-open valves:

Upon air failure, the valve is opened. The valve closes when the signal pressure increases, acting against the force of the springs.

Additional equipment and accessories

For the control valves, the following accessories are available either individually or in combination:

- Positioner
- Limit switch
- Solenoid valves
- Air sets
- Pressure gauge block
- Pneumatic volume booster

Further accessories are available on request to meet customer specifications.

p (bar) 14 12 10 8 6 4 2 t (°C) 0 -10 0 20 40 60 80 100 120 140 150 0 t (°C) -0,5 -1,0 Fig. 3: Pressure-temperature diagram

Pressure-temperature diagram

The range of application is determined by the pressure-temperature diagram. Process data and medium can affect the values in the diagram.

Table 2: General technical data

Nominal size	DN 6 15		
Nominal pressure	PN 10		
Temperature range	See pressure-temperature diagram		
Characteristic	Equal percentage ¹⁾ / linear		
Leakage rate	Leakage rate A acc. to DIN EN 12266-1, P12 (leakage rate 1 BO acc. to DIN 3230 Part 3)		
Rangeability	30:1		
Flanges	DIN EN 1092-2, Form B		

¹⁾ kvs 0,1 and larger

Table 3: Material

Body	Pure PTFE			
Casing	EN-JS 1049 (GGG 40.3)			
Bonnet flange	EN-JS 1049 (GGG 40.3)			
Valve plug	PTFE ²⁾ optionally tantalum or other metals			
Valve seat	PTFE optionally tantalum or other metals			
Bellows PTFE				
Bearing bushing PTFE with carbon				
Packing PTFE V-ring packing loaded by spring washers				
Plug stem 1.4571				
Coating	Two-component polyurethane coating, grey beige, (RAL 1019)			

²⁾ Control insert in tantalum or other metals for 2 mm seat diameter

Table 4:	z values o	depending o	on kvs v	alue, nomin	al size an	d seat diameter
----------	------------	-------------	----------	-------------	------------	-----------------

D	N		6	8 10 15								
Seat ø	in mm	2 ³⁾	2 ³⁾ 6 2 ²⁾ 6 2 ³⁾ 6 10 2 ³⁾ 6 10 13					13				
Travel	in mm		10									
KVS	CV					Acoustic	al valve coe	fficient z				
0.005	0.006	0.9		0.9		0.92			0.92			
0.01 0.03 0.05 0.1	0.01 0.04 0.06 0.12	0.85		0.85		0.9			0.9			
0.1 0.16 0.25 0.63 1.0	0.12 0.19 0.29 0.74 1.17		0.6		0.6		0.65			0.65		
1.6 2.5	1.9 2.9							0.6			0.6	
3.5	4.0											0.55

³⁾ Linear characteristic only with 2 mm seat diameter

Terms for control valve sizing

According to IEC 60534-2-1:

FL = 0.96 xT = 0.75

Correction terms

- For gases and vapours : $\Delta LG = 0$,
- For liquids: $\Delta LF = 0$

i Note		
Only actu	ators with double-sided stroke limitation use!	

Table 5: Permissible differential pressures Δp

A. t t					STAF		ST	EF	
	0.2 1.0	0.4 1.2	0.4 2.0	0.2 .	1.0				
:	Signal pressure ran	ge (travel = 10 mm))	0.2 0.8	0.4 1.0	0.4 1.6	0.4 .	1.0	
				Requi	red supply pre	essure	Max. supp	Max. supply pressure	
Supply pressure			1.3	1.4	2.3	1.2	1.4		
DN	kvs	Seat in mm	Actuator in cm ²			Δp with p2 = 0)		
			120	10	-	-	10	-	
	0.005 0.1	2	175v2	10	-	-	10	-	
/ 15			240	10	-	-	10	-	
0 ID	0.1 1.0	6	120	4	10	10	4	10	
			175v2	10	-	-	10	-	
			240	10	-	-	10	-	
			120	-	10	10	-	10	
10 15	1.6 2.5	10	175v2	9	10	-	9	10	
			240	10	-	-	10	-	
			120	-	10	12	-	10	
15	3.5	13	175v2	3	10	-	3	10	
			240	10	10	10	10	10	

Table 5a: Valves with fail-close actuator Valve with signal pressure 0 bar closed.

Table 5b: Valves with fail-open actuator Valve with required signal pressure closed.

The shaded columns of the table show the standard values. The differential pressures in the white columns of Table 5a apply to liveloaded springs. The permissible differential pressures quoted are only valid for soft-sealed valves.

Dimensions and weights



Table 6: Dimensions and weights for Type O6a Micro-flow Valve

DN		6	8	10	15			
FTF		130	130 130		130			
L2		65	65	65	65			
	SAMSON Type 3271	H2 + H						
H1	SAMSON Type 3277	H2 + H4						
	SAMSON Type 3273	H2 + H3						
H2		269	269	269	265			
Hs		156	156	156	156			
ØD		Ø90	Ø90	Ø90	Ø95			
Ød		Ø14 Ø14		Ø14	Ø14			
Øk		Ø60	Ø60	Ø60	Ø65			
Weig	ght of valve in kg	4	4	4	4			

Table 7: Dimensions and weights for Type 3271 and Type 3277 Pneumatic Actuators

Actuator in cm ²	120	175v2	240	
ØA	168	215	240	
Н	70	78	62	
H4	158	179	166	
H6	75	75	75	
a	G 1/8"	G 1⁄4″	G 1⁄4″	
Weight of Type 3271	2.5	6	5	
Weight of Type 3277	3.2	10	9	

Table 8: Dimensions and weights for Type 3273 Hand-operated Actuator

ØAı	180
НЗ	110
Weight of Type 3273	2

Selection and sizing of the control valve

- 1. Calculate the appropriate kvs coefficient acc. to IEC 60534
- 2. Select the valve size and kvs coefficient from Table 4
- 3. Determine the permissible differential pressure, select the appropriate actuator from Tables 5a and 5b
- 4. Check the application based on the pressure-temperature diagram
- 5. Additional equipment

Ordering text

BR 06a Micro-flow Valve Nominal size: Nominal pressure: Flow coefficient: kvs Characteristic: equal percentage / linear Body: EN-JS 1049/white PTFE Flange design: Form C/F, groove Special design:

Actuator: SAMSON Type, cm² Control pressure range: bar Fail-safe position:

Limit switch (brand name): Solenoid valve (brand name): Positioner (brand name):

Others:

Associated data sheets

For Pneumatic actuator

► T8310-1 bis T8310-3 from SAMSON

i Note

All relevant details regarding the version ordered, which deviate from the specified version in this technical description data, can be taken, if required, from the corresponding order confirmation.